Specification Summary

Reference: QU00000003791 Rev: 2

Purchaser: RedSky Emergency Vehicles

Contact: Kirsten Skyba

Address: 1240 E. Locust Street, Suite 203

Ontario, CA 91761

Sales Contact: Kirsten Skyba

Mobile: 304.839.4051 Phone: 866.500.5948 **Opportunity:** Stock CCL-150 Type 1 – KG - F21P-20301

Account Contact: Address:

Name Specifications
CCL150 • Aluminum



- Aluminum Extruded Body Construction
- CrestCoat Powder Coating Technology
- Aluminum Cabinets
- Multiplex Electrical System
- Flush Mount Windows
- CrestClean Antimicrobial Coating

Sales Options by Category

Base		
Item Number	Name/Description	Quantity
BAS_REG_11	Admin fee	1.00
	Sales Administration Charge	
BAS_VEH_12	TYPE I - CCLP150	1.00
	TYPE I - CCLP150	
BAS_CHA_13	Conversion for an F350 4x4 diesel chassis	1.00
	Conversion for an F350 4x4 diesel chassis	
BAS_CNV_12	72in Interior Headroom	1.00
	72in Interior Headroom	
Chassis		
Item Number	Name/Description	Quantity
CHA_MOD_15	Ford F350 chassis cab 4x4 diesel	1.00
	Ford F350XLT Super Duty Diesel Chassis Cab 4X4 169 6.7L POWER STROKE V8 Diesel	
	Engine Wheelbase 169" (4293 mm) GVWR (Gross vehicle weight rating) 13,300 Lbs /	
	6,033 Kg	
CHA_SYS_11	Anti-theft	1.00
	Anti-theft security system	

CHA_SYS_12	High Idle	1.00
CHA_MIR_11	High Idle system OEM chassis mirrors	1.00
CHA_WIII_II	OEM chassis mirrors	1.00
CHA_PRT_11	Running Boards	1.00
	Diamond-plate aluminum running boards with grip strut	
CHA_PRT_12	F-series chrome wheel simulators	1.00
	Chrome wheel simulators	
CHA_SEC_11	Hidden front grille door unlock switch	1.00
	Hidden front grille door unlock switch	
CHA_SUS_11	LiquidSpring Suspension	1.00
D.: C	LiquidSpring Suspension System - Type 1	
Drivers Compa		
Item Number	Name/Description	Quantity
DRV_CON_15	Control center with pictogram labelled switches	1.00
	Control center with switches and LED backlit pictograms on console	
DRV_SEA_12	Manual adjustment seat	1.00
DD1/ D40 40	OEM manually adjustable chassis seats.	1.00
DRV_PAS_12	Talk-through with sliding window	1.00
DDV CON 13	Cab to module talk-through opening with sliding window	1 00
DRV_CON_12	Chassis voltmeter and conversion voltmeter	1.00
DRV_CON_13	OEM chassis voltmeter. Digital conversion voltmeter on driver's console. Patient status indicator lights	1.00
DKV_CON_13	Patient status indicator lights (Red/Yellow/Green) on driver's console	1.00
DRV_CON_18	Ram mount console	1.00
DRV_CON_ID	Ram mount console	1.00
DRV_CON_14	Door indicator light	1.00
	"Door ajar" and "Compartment" indicator light on driver's console	
DRV_CON_16	Two USB charging outlets	1.00
	Two USB charging outlets on driver's console	
DRV_MAP_12	No floor mount console	1.00
	No floor mount console	
DRV_LIT_11	Passenger reading light	1.00
	Ceiling mount red/white LED reading light centered over passenger seat	
Conversion		
Item Number	Name/Description	Quantity
CON_CS1_11	C1 Compartment, ALS Access and Battery Compartment	1.00
	C1 Compartment - ALS inside/outside access with a sealed battery storage area	
CON_CS1_12	Battery slide-out tray	1.00
	Battery slide-out tray in C1 compartment	
CON_CS2_11	C2 Side Entrance Door	1.00
	C2 - Side entrance door with tinted flush mount window	
CON_CS2_12	Dual step entry with step well light	1.00
	Two-step interior access with LED step well light	
CON_CS3_11	C3 Compartment, Equipment Storage	1.00
CON CC2 42	Open storage in C3 Compartment	1.00
CON_CS3_12	C3 - Backboard storage	1.00
	Dual backboard storage with straps, two adjustable shelves for equipment bags, and	
CON 661 11	stair chair storage in C3 Compartment.	1.00
CON_SS1_11	S1 Compartment - Main Oxygen Storage Main oxygen storage in S1 Compartment	1.00
	Main oxygen storage in 31 compartment	

CON_SS2_11	S2 Compartment - ECC Floatrical Control Control (ECC) with lower againment storage in S2 Compartment	1.00
CON_SS2_12	Electrical Control Center (ECC) with lower equipment storage in S2 Compartment ECC cover Aluminum panel in ECC compartment to cover and protect electrical from water and	1.00
	debris	
CON_SS3_13	S3 Compartment, Outside access closed off	1.00
CON_SS3_12	Equipment storage with outside access closed off in S3 compartment Two adjustable shelves	1.00
CON_555_12	Two adjustable shelves in S3 Compartment	1.00
CON_RDR_11	50/50 Rear doors	1.00
CON_PRT_18	50/50 Split rear entry doors with flush mounted tinted windows Black rubber fenderettes	1.00
CON_PRI_18	Flexible black rubber fenderettes over rear wheels	1.00
CON_PRT_12	Rear kick plate with no text	1.00
	Rear kick plate with no text	
CON_PRT_13	Aluminum rub-rails on each side	1.00
	Aluminum rub-rails on each side of conversion	
CON_PRT_14	Undercoating protection	1.00
	Undercoating protection	
CON_PRT_15	Rear mudguard	1.00
CON DDT 1C	Rear mudguard	1 00
CON_PRT_16	Rear bumper underbody Rear bumper underbody	1.00
CON_PRT_17	Module front corner stone guard	1.00
CON_PRI_17	Module front corner stone guard aluminum checker-plate protection	1.00
CON_PRT_20	Stainless steel fuel fill protector	1.00
00.1 <u>_</u> <u>_</u> 0	Stainless steel protection plate below fuel fill housing	2.00
CON_LIC_11	Flush license plate with LED light	1.00
	Flush license plate with LED light	
Exterior Lighting		
Item Number	Name/Description	Quantity
LIT_IDL_11	Clearance lights	1.00
	Clearance lights - Seven amber and seven red LED marker lights	
LIT_IDL_12	Two 3/4 inch red LED mid-body side lights at rear	1.00
	Two 3/4 inch red LED mid-body side lights at rear to be marker top with turn signal	
LIT DOT 11	below	1 00
LIT_DOT_11	Two red LED brake/tail lights Two red LED brake/tail lights	1.00
LIT_DOT_12	Two amber LED turn lights	1.00
11_001_12	Two amber LED turn lights	1.00
LIT_DOT_15	Two white LED reverse lights	1.00
	Two white LED reverse lights	
Emergency Syst	rems	
Item Number	Name/Description	Quantity
EMG_ACC_12	Chrome bezels	1.00
	M-Series chrome bezels	
EMG_LNS_11	Clear lens	1.00
	Emergency lights to have clear lenses	
EMG_FRL_16	Seven Whelen M9-Series emergency lights	1.00
	Seven Whelen M9-Series emergency lights (Red / Red / Red / White \ Red \ Red \ Red)	
	on front of conversion	

EMG_INL_12	Two Whelen M7-Series red lights, one each side	1.00
5N40 ODL 40	Two Whelen M7-Series red intersection lights, one each side of chassis	4.00
EMG_GRL_12	Two Whelen LING Series red lights	1.00
EMG_USL_12	Two Whelen LIN6 Series red lights Four Whelen M9-Series red lights (two each side)	1.00
EIVIG_U3L_12	Four Whelen M9-Series red lights (two on each side of conversion)	1.00
EMG_LSL_12	Mid Body M7-Series above rear wheel	1.00
LIVIO_LUC_12	Two Whelen M7-Series red lights above rear wheel, one each side	1.00
EMG_USL_13	Four Whelen M9-series LED scene lights	1.00
	Four Whelen M9-series LED scene lights (two on each side of conversion)	
EMG_REL_16	Two Whelen M9-Series and one M7-Series lights	1.00
	Two Whelen M9-Series and one M7-Series lights (Red / Amber \ Red) on rear of	
	conversion	
EMG_REL_15	Two Whelen M6-Series LED load lights	1.00
	Two Whelen M6-Series LED load lights on rear of conversion	
EMG_REL_17	Two Whelen M9-Series red lights at window height	1.00
	Two Whelen M9-Series red lights at window height on rear of conversion	
EMG_SIR_11	Siren amplifiers (100 watt)	1.00
5146 SDV 43	100 Watt Siren amplifier with 4 tones and public address (P/A) microphone	4.00
EMG_SPK_12	Two siren speakers in front bumper	1.00
Interior Combain	Two siren speakers in front bumper Type 1	
	le Configuration	
Item Number	Name/Description	Quantity
CSC_SEA_11	Two (2) position squad bench, 6-point harness	1.00
	Two position squad bench with 6-point harness system. Provides ability for second	
	patient transport using backboard. Includes recessed waste and sharps container at head of squad bench.	
CSC_SEC_11	Locking sharps container in squad bench	1.00
C3C_3LC_11	Locking sharps container in squad bench	1.00
CSC_NET_11	Squad safety net	1.00
555_1121_22	Safety restraint net installed forward of curbside seating	2.00
CSC_ALS_11	ALS Compartment	1.00
	Front ALS compartment with two adjustable shelves	
CSC_DRG_11	Drug cabinet	1.00
	Drug cabinet above ALS compartment	
Interior Streets	ide Configuration	
Item Number	Name/Description	Quantity
SSC_STG_12	CPR seat with 6-point harness system	1.00
	CPR seat with 6-point harness system	
SSC_STG_14	Restocking frames	1.00
	Restocking frames with sliding polycarbonate doors	
SSC_TOP_11	Aluminum countertop	1.00
	Aluminum countertop - Powder coated with antimicrobial coating	
Attendant Seat		
Item Number	Name/Description	Quantity
ATT_SEA_11	Rear-facing EVS seat with 3-point seat belt	1.00
ATT 546 44	Rear-facing EVS seamless vinyl seat with 3-point seat belt	
ATT_BAS_11	Box Base with front/rear slider	1.00
Cot Cot C	Box Base with front/rear slider	
Cot Configurati	ON CONTRACTOR OF THE CONTRACTO	

	No. 10 to 1	0
Item Number	Name/Description	Quantity
SRT_COT_16	Stryker universal floor plate only Stryker universal floor plate only	1.00
CDT FLC 1F		1.00
SRT_ELC_15	Pre-wire Power-LOAD Pre-wire Power-LOAD	1.00
CDT DOC 11	Center mount cot configuration	1.00
SRT_POS_11	Center mount cot configuration Center mount cot configuration	1.00
Oxygen	Center mount cot comiguration	
Item Number	Name/Description	Quantity
	<u> </u>	
OXG_TYP_11	Quick disconnect style outlet	1.00
OVC MPD 12	Quick disconnect style outlet	1.00
OXG_MBR_12	O2 to Go oxygen loading system	1.00
OXG_ACC_11	O2 to Go oxygen loading system with detachable ramp Cylinder changing wrench	1.00
ONG_ACC_II	Cylinder changing wrench with footman loop assembly in oxygen compartment	1.00
OXG_REG_11	Manual oxygen regulator (50PSI)	1.00
ONG_KEG_II	Manual oxygen regulator (50PSI)	1.00
OXG_OUT_11	One oxygen outlet in Action Area	1.00
OXG_001_11	One oxygen outlet in Action Area	1.00
OXG_OUT_13	One oxygen outlet in Action Area One oxygen outlet on curbside wall	1.00
OXG_001_13	One oxygen outlet on curbside wall	1.00
OXG_FLW_11	Flow meter (0-15LPM)	1.00
0x0_12W_11	Oxygen flow meter (0-15LPM) for Action Area outlet	1.00
OXG_FLW_12	Flow meter (0-15LPM)	1.00
0x0	Oxygen flow meter (0-15LPM) for curbside outlet	1.00
OXG_PBR_12	Two D/E cylinder brackets on side entry door	1.00
0/10_1 011	Two D/E portable tank brackets on side entry door	
Electrical	. , , ,	
Item Number	Name/Description	Quantity
ELC_SYS_11	Multiplex system	1.00
	Multiplex electrical system using toggle switches with LED backlit pictogram.	1.00
ELC_SYS_12	Curbside switch panel	1.00
	Curbside switch panel	
ELC_SYS_18	Multiplex system interface cable	1.00
	Multiplex system interface cable for remote diagnosis	
ELC_SYS_14	Rear speaker volume control	1.00
	Rear speaker volume control at Action Area	
ELC_SYS_15	Temperature control with automatic setting	1.00
	•	
	Temperature control with automatic setting at Action Area.	
ELC_SYS_16	Temperature control with automatic setting at Action Area. Patient status indicator lights	1.00
ELC_SYS_16	· · · · · · · · · · · · · · · · · · ·	1.00
ELC_SYS_16 ELC_SYS_17	Patient status indicator lights	1.00
	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area.	
	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area. On/off LED reading light	
ELC_SYS_17	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area. On/off LED reading light On/off LED reading light above Action Area.	1.00
ELC_SYS_17	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area. On/off LED reading light On/off LED reading light above Action Area. Four antenna ports with pre-wiring	1.00
ELC_SYS_17 ELC_ANT_11	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area. On/off LED reading light On/off LED reading light above Action Area. Four antenna ports with pre-wiring Four antenna ports with pre-wiring for antenna RG 58 A/U	1.00
ELC_SYS_17 ELC_ANT_11	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area. On/off LED reading light On/off LED reading light above Action Area. Four antenna ports with pre-wiring Four antenna ports with pre-wiring for antenna RG 58 A/U Two OEM batteries Two OEM batteries Additional 3rd battery	1.00
ELC_SYS_17 ELC_ANT_11 ELC_BAT_11 ELC_BAT_12	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area. On/off LED reading light On/off LED reading light above Action Area. Four antenna ports with pre-wiring Four antenna ports with pre-wiring for antenna RG 58 A/U Two OEM batteries Two OEM batteries Additional 3rd battery Additional 3rd battery	1.00 1.00 1.00
ELC_SYS_17 ELC_ANT_11 ELC_BAT_11	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area. On/off LED reading light On/off LED reading light above Action Area. Four antenna ports with pre-wiring Four antenna ports with pre-wiring for antenna RG 58 A/U Two OEM batteries Two OEM batteries Additional 3rd battery Additional 3rd battery Back up alarm	1.00 1.00 1.00
ELC_SYS_17 ELC_ANT_11 ELC_BAT_11 ELC_BAT_12	Patient status indicator lights Patient status indicator lights (Red/Yellow/Green) at Action Area. On/off LED reading light On/off LED reading light above Action Area. Four antenna ports with pre-wiring Four antenna ports with pre-wiring for antenna RG 58 A/U Two OEM batteries Two OEM batteries Additional 3rd battery Additional 3rd battery	1.00 1.00 1.00 1.00

ELC_BUA_12	Back up alarm override switch	1.00
LLC_BOA_12	Back-up alarm override switch	1.00
ELC_LIT_13	High intensity LED compartment rope lights	1.00
	High intensity LED compartment rope lights	
ELC_LIT_12	Six LED dome lights	1.00
	Six LED dome lights with multiple intensity settings	
ELC_SFT_13	Driver intention indicator lights	1.00
ELC INV 12	Driver intention indicator lights in rear ceiling of conversion	1 00
ELC_INV_12	Xantrex Freedom XC pure sine-wave inverter/charger Xantrex Freedom XC pure sine-wave inverter/charger	1.00
ELC_SHR_14	Auto Eject - Yellow 20 amps	1.00
	Auto-eject shoreline outlet - 120V 20 amp assembly with a yellow waterproof cover	1.00
ELC_SHR_13	Shoreline light	1.00
	Indicator light above the shoreline plug to show power connection	
ELC_ACO_11	1 120V GFCI outlet in Action Area	1.00
	One Hospital-grade 120 VAC GFCI dual outlet with indicator light in Action Area	
ELC_ACO_14	1 120V outlet on lower curbside wall	1.00
	One Hospital-grade 120 VAC dual outlet with indicator light on lower curbside wall	
ELC_ACO_15	1 120V outlet in upper ALS area	1.00
ELC_DCO_11	One Hospital-grade 120 VAC dual outlet with indicator light in upper ALS area One 12 VDC outlet in lower ALS area	1.00
ELC_DCO_II	One 12 VDC outlet in lower ALS area One 12 VDC outlet in lower ALS area	1.00
ELC_DCO_12	One 12 VDC outlet in Action area	1.00
110_000_11	One 12 VDC outlet in Action area	1.00
ELC_CAM_11	Camera monitor in cab	1.00
	Camera monitor in cab	
ELC_CAM_12	Back-up camera	1.00
	Back-up camera	
ELC_SUC_11	Rico RS4X disposable suction system	1.00
1014	Rico RS4X disposable suction system in Action Area	
HVAC		
Item Number	Name/Description	Quantity
HVC_PRI_11	Combo heat and AC	1.00
LIVE ALLY 12	Combo heat and air conditioning with exhaust fan for contaminated air Front mounted condenser	1 00
HVC_AUX_12	Front mounted condenser Front mounted condenser	1.00
Accessories	Tront mounted condenser	
Item Number	Name/Description	Quantity
ACC_INF_23	HEPA air filtration system	1.00
ACC_INF_25	HEPA air filtration system with filter. Designed to filter the air in the cabin and in the	1.00
	sanitary compartment of ambulances, removing 99.995% particulates corresponding to	
	SARS/COVID-19 and reducing the risk of infection.	
ACC_CLK_12	Recessed digital clock above rear entry doors	1.00
	Digital clock recessed above rear entry doors	
ACC_FIR_11	No fire extinguisher in chassis	1.00
	No fire extinguisher in chassis cab	
ACC_FIR_12	No fire extinguisher in S3 compartment	1.00
	No fire extinguisher in S3 compartment	
ACC_GRB_13	L-shaped yellow grab bar on side entry door	1.00
ACC CPP 14	L-shaped yellow grab bar on side entry door	1.00
ACC_GRB_14	L-shaped yellow grab bars on rear entry doors	1.00

	L-shaped yellow grab bars on rear entry doors	
ACC_GRB_11	One 61in ceiling mounted grab rail	1.00
	One 61in ceiling mounted yellow grab rail	
ACC_IVH_14	Four clip style IV hangers with strap	1.00
	Four clip style IV hangers with strap (2 curbside wall, 2 streetside wall)	
ACC_WST_11	Spare plastic trash liners	1.00
	Twelve spare plastic trash liners	
Finish and Trim		
Item Number	Name/Description	Quantity
FIN_PWD_11	Interior powdercoated white	1.00
	Cabinets, wall panels and ceiling are white powder-coated aluminum	
FIN_UPH_13	Grey upholstery	1.00
	Grey vinyl upholstery with yellow head bolster pads on entry doors	
FIN_FLR_11	Floor : Slip resistant, rolled-up 5 in. (127mm)	1.00
	Floor : Slip resistant, rolled-up 5 in. (127mm)	
FIN_FLR_13	Lonplate II Midnight #443TXM	1.00
	Lonplate II Midnight #443TXM flooring	
FIN_TRA_11	Clear anti-slip spray	1.00
	Clear anti-slip spray applied to side entry steps	
FIN_PRT_11	Stainless steel wall protection from cot	1.00
	Stainless steel wall protection on lower streetside cabinet and on lower squad bench	
Paint and Graphics		
Item Number	Name/Description	Quantity

DEC_PWD_11

Powdercoat module white

Powdercoat entire module white to match the chassis

1.00